


Sterilizzatore per guanti

Sterilizer for gloves



**Un'aiuto
concreto
per la
H.A.C.C.P.**

*A practical
help for the
H.A.C.C.P.
rules*



GAMAR

Sterilizzatore per guanti

Sterilizer for gloves

PRINCIPIO DI FUNZIONAMENTO

Una lampada emette dei raggi ultravioletti germicidi, che trasformano l'ossigeno in ozono, distruggendo così i batteri per ossidazione.

L'effetto dell'irraggiamento U.V. 253. Nm. non necessita più di dimostrazione.

È totalmente battericida, virulicida, germicida, ecc.

Gli sterilizzatori generatori di ozono assicurano così un'eccellente decontaminazione dei guanti.

Questi sterilizzatori, conformi alle norme d'igiene, trovano la loro applicazione in tutti i settori dell'industria e dei commerci alimentari.

Costruiti in acciaio inox 18/10, sono concepiti per durare e per essere installati in ambienti eventualmente anche umidi.

UTILIZZO

Dopo aver pulito i guanti, collocarli sull'apposito supporto e azionare il timer.

Alla fine i guanti saranno sterilizzati e pronti all'uso.

CARATTERISTICHE

Cofanatura in acciaio inox 18/10

Timer

Lampada u.v. 253.7 nm

Sportello in plexiglas trasparente sfumato

Chiusura magnetica

MODELLO	ARM 20
---------	--------

DIMENSIONI

ALTEZZA	624 mm
---------	--------

LARGHEZZA	400 mm
-----------	--------

PROFONDITÀ	140 mm
------------	--------

PESO	8 kg
------	------

FUNCTIONING PRINCIPLE

A lamp releases germicide UV rays transforming oxigen into ozone and destroying bacteria by means of oxidation. The effect of the 253 Nm. UV rays exposure does not need to be proved anymore. It totaly kills all kinds of germs, viruses, bacteria, etc...

The ozone-generating sterilizers ensure in this way an excellent decontamination of the gloves.

These sterilizers, complying with all hygiene-related rules, can be applied in any field of industry and food trade.

Built in 18/10 stainless steel, they are especially studied to last a long time and can also be installed in possible humid environments.

USE

After having cleaned the gloves, place them on the support and start the timer. After the required time the gloves will be sterilized and ready for use.

FEATURES

18/10 Stainless steel casing

Timer

U.V. 253.7 nm Lamp

Transparent shaded plexiglass door

Magnetic lock

MODEL	ARM 20
-------	--------

DIMENSIONS

HEIGHT	624 mm
--------	--------

WIDTH	400 mm
-------	--------

DEPTH	140 mm
-------	--------

WEIGHT	8 kg
--------	------



Gamar srl - Via Modena, 42/a - 42015 Correggio RE - Italy

Tel. ++39 0522 691721 - Fax ++39 0522 642641

www.gamarsrl.it - e-mail: info@gamarsrl.it

